AQ-SPEC

Air Quality Sensor Performance Evaluation Center

Evaluation Summary

Sensor Description

Manufacturer/Model: Ecomesure/EcomSmart

Pollutants: O₃

Time Resolution: 1-min

Type: Electrochemical



Additional Information

Field evaluation report:

http://www.aqmd.gov/aqspec/evaluations/criteriapollutants/field

Lab evaluation report:

http://www.aqmd.gov/aqspec/evaluations/criteriapollutants/laboratory


AQ-SPEC website:


http://www.aqmd.gov/aq-spec

- Overall, the accuracy of the Ecomesure EcomSmart sensors ranged from 14.6% to 93.9% and decreased as O₃ conc. increased over the tested concentration range, except at the first steady state. Overall, the sensors overestimated the O₃ measurements < 50 ppb and underestimated higher O₃ levels as compared to FEM T400 in the laboratory experiments at 20°C and 40% RH.
- The Ecomesure EcomSmart sensors exhibited high precision for all T/RH combinations and all O₃ concentrations.
- The Ecomesure EcomSmart sensors (IDs: 0532, 0533) showed low to moderate intra-model variability in the field and laboratory evaluations.
- Data recovery was \sim 96% 100% from all units in both field and laboratory evaluations. Unit 0531 did not transmit data during the lab O_3 evaluations.
- The Ecomesure EcomSmart sensors showed moderate correlations (0.62 < R² < 0.65, 5-min mean) with the corresponding FEM T400 data in the field evaluation and strong correlations with the FEM T400 in the laboratory evaluations (R² \sim 0.87).
- The same three Ecomesure EcomSmart units were tested both in the field (1st stage of testing) and in the laboratory (2nd stage of testing).

Field Evaluation Highlights

- Deployment period 03/10/2022 to 05/10/2022: the three Ecomesure EcomSmart sensors showed moderate correlations with the corresponding FEM O₃ data.
- The units exhibited low intra-model variability and data recovery for O₃ measurements was ~96% from all units.





Coefficient of Determination (R^2) quantifies how the three sensors followed the O_3 concentration change by the reference instruments.

An R² approaching the value of 1 reflects a near perfect agreement, whereas a value of 0 indicates a complete lack of correlation.

Laboratory Evaluation Highlights

Accuracy (O₃)

A (%) =
$$100 - \frac{|\bar{X} - \bar{R}|}{\bar{R}} * 100$$


Steady State (#)	Sensor Mean (ppb)	FEM T400 (ppb)	Accuracy (%)
1	52.9	28.5	14.6
2	50.4	47.5	93.9
3	66.8	88.6	75.4
4	102.2	150.6	67.9
5	164.7	257.0	64.1


Accuracy was evaluated by a concentration ramping experiment at 20°C and 40% RH. The sensor's readings at each ramping steady state are compared to the reference instrument.


A negative % means sensors' overestimation by more than two fold. The higher the positive value (close to 100%), the higher the sensor's accuracy.



Precision (O₃)








100% represents high precision.

Sensor's ability to generate precise measurements of O₃ concentration at low, medium, and high pollutant levels were evaluated under 9 combinations of T and RH, including extreme weather conditions like cold and dry (5°C and 15% RH) cold and humid (5°C and 65% RH), hot and humid (35°C and 65% RH), or hot and dry (35°C and 15% RH).

Coefficient of Determination



The Ecomesure EcomSmart sensors showed strong correlations with the corresponding FEM T400 O_3 data ($R^2 \sim 0.87$) at 20°C and 40% RH.

Climate Susceptibility

From the laboratory studies, temperature and relative humidity had minimal effect on the Ecomesure EcomSmart sensors' ozone measurements.

Observed Interferents

 NO_2



All documents, reports, data, and other information provided in this document are for informational use only. Mention of trade names or commercial products does not constitute endorsement or recommendation. As a Government Agency, the South Coast AQMD and its AQ-SPEC program highly recommend interested entities to make use and purchase decisions based on the requirements of their study design, the technical aspects and features of their specific project applications.